

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/11 mm

Order data

Order number	260340 25/11
GTIN	4045197877833
Item class	21T

Technical description

Centre offset L_3	17 mm
ISO code toolholder	A25R SDQCR/L11
Setting angle κ	107.5 degrees
Pack of insert screws	269028 8
Insert size	11 mm
Overall length L	200 mm
Overhang L_1	75 mm
Clamping height L_2	24 mm
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	32.5 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500