

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 12/07mm**

**Order data**

Order number	260341 12/07
GTIN	4045197877871
Item class	21T

**Technical description**

Overhang $L_1$	36 mm
Overall length $L$	140 mm
Centre offset $L_3$	9 mm
Insert size	7 mm
Pack of insert screws	269028 7
ISO code toolholder	A12L SDQCR/L07
Minimum pre-drill $\varnothing D_{\min}$	17 mm
Setting angle $\kappa$	107.5 degrees
suitable indexable insert	DC.. 0702..
Clamping height $L_2$	11 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500