

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	260341 20/11
GTIN	4045197877895
Item class	21T

Technical description

Overhang L_1	60 mm
Pack of insert screws	269028 8
Insert size	11 mm
ISO code toolholder	A20R SDQCR/L11
Centre offset L_3	13 mm
Overall length L	200 mm
suitable indexable insert	DC.. 11T3..
Clamping height L_2	18 mm
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500