

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	260344 20/11
GTIN	4045197877956
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 8
ISO code toolholder	A20R SDXCR/L11
Head length L_1	40 mm
Clamping height L_2	18 mm
Insert size	11 mm
Overall length L	200 mm
Centre offset L_3	13 mm
Setting angle κ	93 degrees
Usable depth T	10 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500