

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 25/11 mm**

**Order data**

Order number	260344 25/11
GTIN	4045197877963
Item class	21T

**Technical description**

ISO code toolholder	A25R SDXCR/L11
Clamping height $L_2$	23 mm
Setting angle $\kappa$	93 degrees
Centre offset $L_3$	17 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Overall length L	200 mm
Insert size	11 mm
Head length $L_1$	50 mm
Usable depth T	10 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500