

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 20/11 mm**

**Order data**

Order number	260345 20/11
GTIN	4045197877994
Item class	21T

**Technical description**

Pack of insert screws	269028 8
Centre offset $L_3$	13 mm
Clamping height $L_2$	18 mm
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Head length $L_1$	40 mm
Setting angle $\kappa$	93 degrees
ISO code toolholder	A20R SDXCR/L11
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Usable depth T	10 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500