

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 25/11 mm

Order data

Order number	260345 25/11
GTIN	4045197878007
Item class	21T

Technical description

Insert size	11 mm
Setting angle κ	93 degrees
Overall length L	200 mm
Centre offset L_3	17 mm
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Clamping height L_2	23 mm
Pack of insert screws	269028 8
Head length L_1	50 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A25R SDXCR/L11
Usable depth T	10 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500