

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	261132 20/11
GTIN	4045197878021
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	VB.. 1103..
Setting angle κ	93 degrees
Head length L_1	20.5 mm
Pack of insert screws	269028 7
Overall length L	200 mm
ISO code toolholder	A20R SVUBR/L11
Centre offset L_3	13 mm
Clamping height L_2	18 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500