

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 40/16mm

Order data

Order number	261133 40/16
GTIN	4045197878106
Item class	21T

Technical description

suitable indexable insert	VB.. 1604..
Head length L_1	40 mm
Centre offset L_3	27 mm
Shim screw	269013 2
Setting angle κ	93 degrees
Shim	269005 8
Pack of insert screws	269028 2
Insert size	16 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Clamping height L_2	39 mm
Overall length L	300 mm
ISO code toolholder	A40T SVUBR/L16
Shank $\varnothing D_s$	40 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Shim screw Type 2	269013 2
Shim Type 8	269005 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500