

Garant
Screw-on toolholder, right-hand, Shank / insert size: 25/12mm

Order data

Order number	260704 25/12
GTIN	4045197878137
Item class	21T

Technical description

Pack of insert screws	269028 20
Functional width L ₄	22 mm
suitable indexable insert	SC.. 1204..
ISO code toolholder	SSBCR/L 2525M12
Shank size	25 mm
Insert size	12 mm
Shim screw	269013 5
Shim	269005 9
Head length L ₁	20 mm
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Shim Type 9	269005 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500