

Garant
Screw-on toolholder, left-hand, Shank / insert size: 16/09mm

Order data

Order number	260705 16/09
GTIN	4045197878144
Item class	21T

Technical description

Insert size	9 mm
Pack of insert screws	269028 2
Overall length L	100 mm
ISO code toolholder	SSBCR/L 1616H09
Shank size	16 mm
Shim	269005 12
Functional width L ₄	13 mm
Shim screw	269013 2
Head length L ₁	20 mm
suitable indexable insert	SC.. 09T3..
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw Type 2	269013 2
Shim Type 12	269005 12
Set of insert screws Type 2	269028 2
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500