

Garant
Screw-on toolholder, left-hand, Shank / insert size: 20/12mm

Order data

Order number	260705 20/12
GTIN	4045197878151
Item class	21T

Technical description

Pack of insert screws	269028 20
Functional width L ₄	17 mm
ISO code toolholder	SSBCR/L 2020K12
Head length L ₁	20 mm
Overall length L	125 mm
suitable indexable insert	SC.. 1204..
Insert size	12 mm
Shim screw	269013 5
Shim	269005 9
Shank size	20 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Set of insert screws Type 20	269028 20
Shim Type 9	269005 9
Shim screw Type 5	269013 5
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500