

Garant
Screw-on toolholder, left-hand, Shank / insert size: 25/12mm

Order data

Order number	260705 25/12
GTIN	4045197878168
Item class	21T

Technical description

suitable indexable insert	SC.. 1204..
Overall length L	150 mm
Head length L ₁	20 mm
Shim screw	269013 5
Insert size	12 mm
Shim	269005 9
Shank size	25 mm
Pack of insert screws	269028 20
ISO code toolholder	SSBCR/L 2525M12
Functional width L ₄	22 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Shim Type 9	269005 9
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500