

Garant
Screw-on toolholder, neutral, Shank / insert size: 08/07mm

Order data

Order number	260300 08/07
GTIN	4045197878229
Item class	21T

Description

Screw-on toolholder 08/07 mm ISO code toolholder: SDNCN 0808D07
 suitable indexable insert: DC.. 0702..
 Functional width L₄ neutral holders: 4 mm
 Overhang L₁ neutral holders: 7.5 mm
 Overall length L neutral holders: 60 mm
 Pack of insert screws: 269028 22

Technical description

Pack of insert screws	269028 22
Overhang L ₁ neutral holders	7.5 mm
Functional width L ₄ neutral holders	4 mm
Insert size	7 mm
Shank size	8 mm
Overall length L neutral holders	60 mm
ISO code toolholder	SDNCN 0808D07
suitable indexable insert	DC.. 0702..
Series	QuickTurn
Application type	neutral
Standard	DIN ISO 5610

Through-coolant	no
Setting angle κ	62.5 °
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Set of insert screws 10 pieces	269440
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15