



## Boring bar set, steel, without IC, right-hand, Type: SET06



### Order data

Order number	260038 SET06
GTIN	4045197878281
Item class	29W

### Description

**Version:**

Without through-coolant feed.

**Supplied with:**

Plastic case

### Technical description

suitable indexable insert	CC.. 0602..
ISO code toolholder	S1012K SCLCR06
ISO code toolholder	S0608H SCLCR06
ISO code toolholder	S0810J SCLCR06
ISO code toolholder	S1216M SCLCR06
Pack of insert screws	269028 7
Head length L <sub>1</sub>	22 mm
Head length L <sub>1</sub>	27 mm

Head length L <sub>1</sub>	33 mm
Head length L <sub>1</sub>	42 mm
Clamping height L <sub>2</sub>	7 mm
Clamping height L <sub>2</sub>	9 mm
Clamping height L <sub>2</sub>	11 mm
Clamping height L <sub>2</sub>	15 mm
Minimum pre-drill Ø D <sub>min</sub>	8 mm
Minimum pre-drill Ø D <sub>min</sub>	11 mm
Minimum pre-drill Ø D <sub>min</sub>	13 mm
Minimum pre-drill Ø D <sub>min</sub>	16 mm
Centre offset L <sub>3</sub>	4 mm
Centre offset L <sub>3</sub>	6 mm
Centre offset L <sub>3</sub>	7 mm
Centre offset L <sub>3</sub>	9 mm
Neck width L <sub>4</sub>	6 mm
Neck width L <sub>4</sub>	8 mm
Neck width L <sub>4</sub>	10 mm
Neck width L <sub>4</sub>	12 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Type of product	Boring bar

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500