



Spring force gauge Macro Line Newton, maximum weighing range: 50N



Order data

Order number	479422 50
GTIN	7612348800490
Item class	47F

Description

Version:

Precision balances with high accuracy $\pm 0.3\%$ of the load. Taring range up to 20% of the capacity. Any measuring position (apart from No. 479410 - only vertical). Zeroing and 20 % tare via the adjustment screw. Top and bottom mountings can be rotated by 360°. With drag pointer and handle.

Supplied with:

Plastic case and instruction manual.

Optional extras:

Conversion kit into spring force gauge No. 479421.

Technical description

Graduation	0.5 N
maximum weighing range	50 N
Scale length	140 mm
Load capacity	Hook

Calibration	K1
Type of product	Spring balance

Services

CalibrationSpring balance Type F	027730 F
----------------------------------	----------

Accessories

Memory pointer Type MACRO	479429 MACRO
Compression set Type MACRO	479421 MACRO