

**Mitutoyo****Digital depth gauge IP 67 with data output, Measuring range: 150mm****Order data**

Order number	418713 150
GTIN	4946368727141
Item class	44A

**Description****Version:**

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Additional extension base No. 418744.

Data cable No. 497085.

**Technical description**

Cross-section measuring beam	16x3.5 mm
Measuring range	0 mm
Bridge length	100 mm
Interface	Digimatic interface
Interface	USB interface
Calibration	A1
Scale divisions	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 357

Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm
Standard	ISO 13385
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

## Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

## Accessories

Connecting cable with data switch Type USB2	497085 USB2
Single extension base Bridge length 320 mm	418744 320
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Single extension base Bridge length 260 mm	418744 260
Connecting cable with data switch Type D2	497085 D2
Single extension base Bridge length 180 mm	418744 180
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D1	497085 D1
Transmitter Type S11E	498966 S11E