

Mitutoyo
Digital external micrometer, Measuring range: 25-50mm

Order data

Order number	421571 25-50
GTIN	4946368716695
Item class	44A

Description
Version:

Error limits more accurate than the requirements of **DIN 863**. Extra large LCD display (7.5 mm). "Function Lock" prevents accidental readjustment of the zero point. **Combination ratchet** (torque limitation in the barrel and in the quick drive) for one-handed use and use in a holder.

Advantage:

Measuring time reduction of up to 40% due to 2 mm spindle pitch.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357. From size 25-50, 1 setting standard.

Technical description

Scale divisions	0.001 mm
Spindle pitch	2 mm
Spindle Ø	6.35 mm
Calibration	B2
Measuring range	25 - 50 mm
Error limit	2 µm
Number of batteries contained	1

Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Button cell / special battery Battery type 357	081560 357
Micrometer setting standard overall length 25 mm	421100 25