



Digital caliper with large display, Measuring range: 200 mm



Order data

Order number	412717 200
GTIN	4059192058326
Item class	43A

Description

Version:

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measurement system, operational life approx. 3 years. The reference-lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With square depth gauge.

Supplied with:

1 battery No. 081560 size CR2032
 Packaging: sturdy box
 Standard: DIN 862
 Reversible reading: mm / inch
 Depth gauge: flat
 Measured value saving: MAHR Reference Lock system
 Calibration: A1
 Scale divisions: 0.01 mm
 Scale divisions: 0.0005 in
 Error limit: 0.03 mm
 Jaw length: 50 mm

Technical description

Measuring range	0 - 200 mm
Digit height LCD display	11 mm
Reversible reading	mm / inch
Scale divisions	0.01 mm

Data sheet

Measured value saving	MAHR Reference Lock system
Depth gauge	flat
Error limit	0.03 mm
Depth gauge available	yes
Scale divisions	0.0005 in
Standard	DIN 862
Jaw length	50 mm
Working time	approx. 3 years
Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------