

**KERN**
**Precision scales, type 572, maximum weighing range: 420g**

**Order data**

Order number	479520 420
GTIN	4045761014152
Item class	47D

**Description**
**Version:**

- **Robust metal casing.**
- **Simple self-explanatory user guide.**
- **Selectable mains and battery operation.**
- **Units of weight (e.g. screw weight) can be freely programmed.**
- **CAL calibration programme: For accuracy adjustment (required external calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces. Display selectable between pieces and weight.**
- **Formulation weighing: Separate memory for weight of the tare vessel and of the formulation ingredients (net totals).**

**Supplied with:**

Mains adapter 230 V / 50 Hz and protective hood.

**Optional extras:**

External battery, data cable, printer on request.

Calibration: Price on request

Scale divisions: 0.001 g

Reproducibility: 0.002 g

Linearity:  $\pm 0.005$  g

Settling time: 3 s

Minimum unit weight: 0.01 g  
Dimensions of weighing plate: Ø 106 mm

## Technical description

Dimensions of weighing plate	Ø 106 mm
Scale divisions	0.001 g
Net weight	2.3 kg
Linearity	± 0.005 g
Manufacturer's designation	572
Width	180 mm
Height	85 mm
Settling time	3 s
Minimum unit weight	0.01 g
maximum weighing range	0 - 420 g
Reproducibility	0.002 g
Depth	310 mm
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Interface	RS232 interface
Calibration	Price on request
Type of product	Precision balance

## Services

Labelling laser-etched Type	018940
-----------------------------	--------