

**BMI**<sup>®</sup>**Tape measure, stainless, Tape length: 3m****Order data**

Order number	462130 3
GTIN	4007368113430
Item class	46M

**Description****Version:****V2A version** with stainless bright measuring tape.

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP<sup>®</sup> material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

**Technical description**

Body length	58 mm
Body width	26 mm
Tape width	13 mm
Body height	57 mm
Standard	EG II

Calibration	G1
Type of product	Measuring tape

**Services**

CalibrationTape measure maximum length 5 m	026240 5
--	----------