

**Tape measure, stainless, Tape length: 5m****Order data**

Order number	462130 5
GTIN	4007368113447
Item class	46M

**Description****Version:**

**V2A version** with stainless bright measuring tape.

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP® material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

Calibration: G1

Standard: EG II

Tape width: 16 mm

Body length: 75 mm

Body width: 26 mm

Body height: 70 mm

**Technical description**

Body length	75 mm
Body width	26 mm

Body height	70 mm
Tape width	16 mm
Standard	EG II
Calibration	G1
Type of product	Measuring tape

## Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
Calibration Tape measure maximum length 5 m	026240 5
5	026250 5