

**BMI**<sup>®</sup>**Tape measure, stainless, Tape length: 8m****Order data**

Order number	462130 8
GTIN	4007368113454
Item class	46M

**Description****Version:****V2A version** with stainless bright measuring tape.

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP<sup>®</sup> material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

**Technical description**

Tape width	19 mm
Body width	32 mm
Body height	77 mm
Band length	8 m
Body length	78 mm

Standard	EG II
Calibration	G1
Type of product	Measuring tape

**Services**

CalibrationTape measure maximum length 10 m	026240 10
---	-----------