



Fine boring head MicroKom® BluFlex® 2



Order data

Order number	238392
GTIN	4047109280205
Item class	27G

Description

Version:

- **Linearity range: -0.2 to +4.4 mm (-0.0079 to 0.1732 inch) on the Ø.**
- **µ-precise display resolution: 0.001 mm on the Ø.**
- **Internal hexagon wrench allows radial adjustment and clamping of the micro-adjustable drilling head.**
- **Modern high-contrast OLED display directly at the micro-adjustable drilling head.**
- **The display can be rotated through 180°.**
- **Easy to operate directly at the touch display.**
- **Additional Bluetooth® low energy interface for easy display on a commercially-available smartphone with Android™ or IOS 7.**
- **Higher speeds thanks to integral partial balancing.**
- **Very sensitive adjustment permits precise infeed.**
- **Absolute travel measuring system – the absolute and relative slide position is output every time the device is switched on.**
- **Universal ABS® port.**
- **Battery easily replaceable.**
- **1: 1 compatible with the available variations of the previous system.**

Through-coolant: yes

Boring range Ø: 6 - 125 mm

Technical description

Boring range Ø	6 - 125 mm
Shank	ABS
Through-coolant	yes
Type of product	Boring tool

Accessories

Bridge for MicroKom® hi.flex and MicroKom BluFlex® 2 Boring range Ø 120-155 mm	238395 120-155
---	----------------