

KERN**Hanging scales type HCB, maximum weighing range: 100Pkg****Order data**

| | |
|--------------|---------------|
| Order number | 479435 100P |
| GTIN | 4045761069022 |
| Item class | 47D |

Description**Version:**

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

Supplied with:

Stainless steel carabiner, stainless steel S-hook (non-standard for size 500 / 1000) and 3 batteries No.081561 size LR6.

Technical description

| | |
|------------------------|------------|
| Scale divisions | 50 g |
| Net weight | 0.6 kg |
| Body height | 150 mm |
| maximum weighing range | 0 - 100 kg |
| Body width | 80 mm |

| | |
|---|---------------------------------|
| Body depth | 45 mm |
| Calibration | K2 |
| Article no of the battery / rechargeable battery fitted | 081561 LR6 |
| Number of batteries contained | 3 |
| Power supply | Battery-powered |
| Manufacturer's designation | HCB |
| Type of product | Suspended scales / crane scales |

Services

| | |
|--|------------|
| Calibration Scales maximum weighing range 100 kg | 027700 100 |
|--|------------|

Accessories

| | |
|---|------------|
| Alkaline-manganese batteries International size LR6 | 081561 LR6 |
|---|------------|