

**HEDI**
**Cable drum plastic for F, B, PL and CZ, Type: 20N2**

**Order data**

Order number	081138 20N2
GTIN	4003644019991
Item class	08B

**Description**
**Version:**

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

Sturdy cable drum of high-impact plastic with **thermal overload protection**.

- **400 V CEE input plug 16 A.**
- **400 V CEE output plug 16 A with spring-loaded cover.**
- **Two 250 V standard Schuko sockets with spring-loaded covers.**
- **Conductor cross-section 2.5 mm.**

**Certified for continuous exterior use and for use in humid environments.**

With 250 V sockets for **F, B, PL, and CZ**.

**Function:**

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with  $\varnothing > 1 \text{ mm}$ , however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Rated power unrolled: 5500 (16 A) W

Cable class: H07RN-F

Cable structure: 5G2.5

Material cable: Neoprene

Cable length: 20 m

## Technical description

Cable class	H07RN-F
Cable structure	5G2.5
IP Index of Protection	IP 44
impact-resistant and splash-proof	Category 2 (K2) to BGI
Material cable	Neoprene
Number of sockets 400 V/16 A	1
Rated power unrolled	5500 (16 A) W
Number of sockets 230 V	2
Cable length	20 m
Type	20N2
Material of body	Plastic
Power supply	Mains operated
Type of product	Cable drum