

KERN**Precision scales, type 572, maximum weighing range: 12100g****Order data**

Order number	479520 12100
GTIN	4045761014282
Item class	47D

Description**Version:**

- **Robust metal casing.**
- **Simple self-explanatory user guide.**
- **Selectable mains and battery operation.**
- **Units of weight (e.g. screw weight) can be freely programmed.**
- **CAL calibration programme: For accuracy adjustment (required external calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces. Display selectable between pieces and weight.**
- **Formulation weighing: Separate memory for weight of the tare vessel and of the formulation ingredients (net totals).**

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

External battery, data cable, printer on request.

Calibration: Price on request

Scale divisions: 0.05 g

Reproducibility: 0.05 g

Linearity: ± 0.15 g

Settling time: 3 s

Minimum unit weight: 0.5 g
Dimensions of weighing plate: 160×200 mm

Technical description

Net weight	2.7 kg
Minimum unit weight	0.5 g
Depth	310 mm
Height	85 mm
Dimensions of weighing plate	160×200 mm
maximum weighing range	0 - 12100 g
Scale divisions	0.05 g
Width	180 mm
Linearity	± 0.15 g
Reproducibility	0.05 g
Settling time	3 s
Manufacturer's designation	572
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Interface	RS232 interface
Calibration	Price on request
Type of product	Precision balance

Services

Labelling laser-etched Type	018940
-----------------------------	--------