



Pneumatic random orbital sander, Type: X61V



Order data

Order number	079656 X61V
GTIN	616026000346
Item class	03R

Description

Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level.

Dynorbital spirit orbital sander (152 mm) for central extraction. **EXTREME** orbital sander series. Very ergonomic and **powerful**. With a 5 mm orbital stroke. Connection for **external extraction**.

Supplied with:

Including the necessary coupling adaptors.

Note:

See No. 567775 for velour abrasive discs.

DynaMaze hook and loop backing pad for No. 079655 and 079656 size X61V and size 58436 can be found under No. 567872 size 150.

maximum speed: 12000 min⁻¹

maximum air consumption: 538 l/min

Backing pad Ø: 150 mm

Type of extraction: External

Stroke: 5 mm

Weight: 0.9 kg

Technical description

Data sheet

Backing pad Ø	150 mm
Weight	0.9 kg
maximum speed	12000 min ⁻¹
maximum vibration to EN	8.78 m/s ²
Operating noise	75 dB(A)
Manufacturer's designation	Extreme 150 mm
Type of extraction	External
maximum air consumption	538 l/min
Stroke	5 mm
Type of product	Orbital sander

Accessories

Hook and loop fastener backing pad DynaMaze Ø 150 mm Manufacturer's designation 22290	079690 22290
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 120	567775 120
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 240	567775 240
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 320	567775 320
PU hook and loop backing pad DynaMaze External Ø 150 mm	567872 150
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 180	567775 180
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 60	567775 60
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 600	567775 600
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 400	567775 400
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 800	567775 800
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 40	567775 40
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 80	567775 80