

**KERN**
**Crane scales type HFB, maximum weighing range: 600 kg**

**Order data**

Order number	479436 600
GTIN	4045761111677
Item class	47D

**Description**
**Version:**

Back-lit LCD display, easily read even from afar. Internal battery (with optical charge display) gives high mobility. Data hold function for retaining the display value.

Character height 25 mm with twin display at the rear. Battery lasts approx. 20 hours.

**Supplied with:**

Remote control with 2 batteries No. 081556 size LR3, mains adapter.

**Attention:**

German version. Order free UK adapter plug No. 08 1174\_GB.

Calibration: Price on request

Scale divisions: 200 g

Error limit from maximum value: 2 %

Body width: 163 mm

Body depth: 126 mm

Body height: 159 mm

Overall length: 390 mm

**Technical description**

Net weight	2.2 kg
------------	--------

Overall length	390 mm
maximum weighing range	0 - 600 kg
Scale divisions	200 g
Body height	159 mm
Error limit from maximum value	2 %
Operating temperature	0 - 40 °C
Body width	163 mm
Body depth	126 mm
Calibration	Price on request
Batteries / rechargeable batteries included	081556 LR3
Number of batteries contained	2
Height of numerals	25 mm
Manufacturer's designation	HFB
Battery working life	20 h

## Services

Labelling laser-etched	018940
------------------------	--------

## Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
---	------------