

KERN**Counting scales, type CXB, maximum weighing range: 15kg****Order data**

Order number	479540 15
GTIN	
Item class	47D

Description**Version:**

- **Precision counting scales with automatic reference optimisation (progressive refinement of the average value of the item weight).**
- **Target item count and target weight programmable to give an acoustic signal.**
- **Cumulative item counter for totalling identical items by total quantity and overall weight.**
- **Reference quantities or reference weight.**
- **Selectable mains and battery operation.**
- **CAL calibration programme: For calibrating the accuracy (requires an external calibration weight which is available on request).**
- **Display switching between items and weight.**

Suitable for weighing plastic parts thanks to the integral **ESD protection**.

Supplied with:

Mains adapter 230 V / 50 Hz, battery and protective hood.

Calibration: K2

Scale divisions: 1 g

Reproducibility: 1 g

Linearity: ± 2 g

Settling time: 2 s

Minimum unit weight: 5 g

Dimensions of weighing plate: 300x225 mm

Technical description

Settling time	2 s
Width	300 mm
Linearity	± 2 g
Dimensions of weighing plate	300×225 mm
Minimum unit weight	5 g
Reproducibility	1 g
Scale divisions	1 g
Height	110 mm
Depth	330 mm
Net weight	4 kg
maximum weighing range	0 - 15 kg
Manufacturer's designation	CXB
Power supply	Rechargeable battery-powered
Calibration	K2
Type of product	Counting balance

Services

Calibration Scales maximum weighing range 50 kg	018920 50
Labelling laser-etched Type	018940
DAkkS calibration Scales maximum weighing range 50	019700 50
Calibration Scales maximum weighing range 50 kg	027700 50
DAkkS calibration Scales maximum weighing range 50	027710 50