

KERN**Counting system, type CCS, maximum weighing range: 150kg**

Order data

Order number	479542 150
GTIN	4045761104624
Item class	47D

Description

Version:

- **Precision counting scales with automatic reference optimisation (progressive refinement of the average value of the item weight).**
- **Target item count and target weight programmable to give an acoustic signal.**
- **Cumulative item counter for totalling identical items by total quantity and overall weight.**
- **Reference quantities or reference weight.**
- **Selectable mains and battery operation.**
- **CAL calibration programme: For calibrating the accuracy (requires an external calibration weight which is available on request).**
- **Display switching between items and weight.**

Counting system consisting of **reference scales and quantity scales (platform scales)** with a 2.0 m connection cable.

Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood for reference scales.

Optional extras:

Internal battery, signal lamp available on request.

Note:

For calibration please select both the items offered, since both the reference scales and also the quantity scales (platform scales) must be calibrated.

Technical description

Platform scales depth	400 mm
Height	125 mm
Dimensions of weighing plate	294×225 mm
Settling time	2 s
maximum weighing range	0 - 150 kg
Platform scales height	137 mm
Width	320 mm
Manufacturer's designation	CCS
Scale divisions	0.1 g
Depth	350 mm
Platform scales width	500 mm
Net weight	16 kg
Reproducibility	0.2 g
Linearity	± 0.2 g
Minimum unit weight	1 g
Reading the quantity scales	5 g
Power supply	Rechargeable battery-powered
Calibration	Price on request
Type of product	Counting balance