

Garant**Screw-on toolholder, neutral, Shank / insert size: 20/12mm****Order data**

| | |
|--------------|---------------|
| Order number | 260711 20/12 |
| GTIN | 4045197880819 |
| Item class | 21T |

Technical description

| | |
|---|-------------------------------|
| Overall length L neutral holders | 125 mm |
| Pack of insert screws | 269028 20 |
| Functional width L ₄ neutral holders | 10 mm |
| Shank size | 20 mm |
| Shim screw | 269013 5 |
| Shim | 269005 9 |
| ISO code toolholder | SSDCN 2020K12 |
| suitable indexable insert | SC.. 1204.. |
| Overhang L ₁ neutral holders | 11.2 mm |
| Insert size | 12 mm |
| Standard | DIN ISO 5610 |
| Application type | neutral |
| Through-coolant | no |
| Setting angle κ | 45 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim Type 9 | 269005 9 |
| Shim screw Type 5 | 269013 5 |
| Set of insert screws Type 20 | 269028 20 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |