



## mobilux LED hand-held illuminating magnifying glass, Type: 4



### Order data

Order number	490818 4
GTIN	4048347280170
Item class	49A

### Description

#### Version:

Aspherical PXM lightweight lens, hard coated with ceratec® on both sides, bright homogeneous illumination by SMD LED and collimation optics. Power control by step-up converter, giving bright and consistent illumination. 3 different light colours can be selected by 2 clip-on filters, supplied.

#### Supplied with:

Supplied with 2 batteries No. 081561 size LR6, 3 clip-on filters, and lens protection case.

Lens length: 75 mm

Lens width: 50 mm

Magnification (x-times): 4

### Technical description

Lens length	75 mm
Magnification (x-times)	4
Lens width	50 mm
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR6
Series	mobilux LED
Power supply	Battery-powered
Type of lens	aspherical
Lighting	SMD-LED

Packaging	Lens protection case
Type of product	Hand-held illuminating magnifying glass

---

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
mobase stand with 1/4 inch tapped hole Type UNI	490817 UNI
Alkaline-manganese batteries International size LR6	081556 LR6