

Garant
**Standard keyway broaching toolholder \varnothing DS 32 mm, from slot width m:
14mm**

Order data

Order number	290358 14
GTIN	4045197881243
Item class	29K

Description
Attention:

Always use the minimum pre-drill \varnothing to match the slot width (e.g. for slot width 14 mm, minimum pre-drill $\varnothing = 38.22$ mm).

Note:

- **Individual holder sizes are for different slot widths. In such cases, where possible, always use the optimum combination of holder and cutting insert (identical size) for maximum stability.**
- **For lathes without Y-axis, please use eccentric bush No. 290391– 290393 for exact setting of the Y-coordinate.**
- **For machining centres, use the alignment aid No. 290397 and a dial indicator to check the spindle orientation.**

Technical description

Min. pre-drilling - \varnothing D _{min}	38.22 mm
Min. pre-drilling - \varnothing D _{min}	38.58 mm
suitable for slot width m	14 mm
suitable for slot width m	16 mm
Reach L ₁	126 mm
Screw	290399 3
Centre offset L ₃	19.5 mm
Shank \varnothing	32 mm

Tool holder $\varnothing D_1$	35 mm
Through-coolant	yes
Shank length L_s	100 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

Accessories

Fastening screw Type 3	290399 3
------------------------	----------