



Abrasive cloth (A) economy roll, brown KK 114 F, 50 mm × 50 m, Grit: 150



Order data

| | |
|--------------|---------------|
| Order number | 557750 150 |
| GTIN | 4018875266755 |
| Item class | 56V |

Description

Version:

Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A)**. Very good grit bonding, high abrasion performance and long service life.

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications**. This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying.

Packaging tape **with integral tear-off cutter**.

Application:

Predominantly for rubbing down metals by hand, but also suitable for all other materials.

Technical description

| | |
|----------------------|------------------------------|
| Grit designation | medium |
| Grit | 150 |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |
| Economy roll width | 50 mm |

| | |
|------------------------|----------------|
| Economy roll length | 50 m |
| Product name attribute | 50 mm × 50 m |
| Type of product | Abrasive cloth |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |