



## Abrasive cloth (A) economy roll, brown KK 114 F, 25 mm × 50 m, Grit: 150



### Order data

|              |               |
|--------------|---------------|
| Order number | 557800 150    |
| GTIN         | 4018875266519 |
| Item class   | 56V           |

### Description

#### Version:

Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A)**. Very good grit bonding, high abrasion performance and long service life.

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications**. This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying.

Packaging tape **with integral tear-off cutter**.

#### Application:

Predominantly for rubbing down metals by hand, but also suitable for all other materials.

### Technical description

|                      |                              |
|----------------------|------------------------------|
| Grit designation     | medium                       |
| Grit                 | 150                          |
| Grinding media       | Standard aluminium oxide (A) |
| Grinding medium code | A                            |
| Economy roll width   | 25 mm                        |

|                        |                |
|------------------------|----------------|
| Economy roll length    | 50 m           |
| Product name attribute | 25 mm × 50 m   |
| Type of product        | Abrasive cloth |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable only under restricted conditions |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| Uni                            | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |