

**Universal abrasive cleaner, 80×50×20 mm, Type: G****Order data**

| | |
|--------------|---------------|
| Order number | 557660 G |
| GTIN | 4045197241757 |
| Item class | 52E |

Description**Version:**

Flexible hand abrasive block with flexibly bonded abrasive grit (long service life, fully usable). Open pore bonding ensures the abrasive body never clogs. Suitable for wet and dry use. Water and oil resistant.

Economy version with aluminium oxide (A).

Application:

Multi-purpose for **cleaning, polishing, smoothing, mat finishing** and **abrading all materials**.

Note:

Water, oil, compounds or similar agents **increase the effectiveness**.

Technical description

| | |
|------------------------|---------------|
| Grit designation | coarse |
| Height | 20 mm |
| Width | 50 mm |
| Length | 80 mm |
| Product name attribute | 80×50×20 mm |
| Type of product | Sanding block |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|--|----------------------|-----------------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Carbide (HM) | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable only under restricted conditions | | |
| Stone | suitable | | |
| Paint | suitable | | |
| wet maximum | suitable | | |
| dry | suitable | | |