



Screwdriver for slot-head, with 2-component SwissGrip handle ESD, Blade width b: 2,5mm



Order data

| | |
|--------------|---------------|
| Order number | 660050 2,5 |
| GTIN | 7610733256075 |
| Item class | 63E |

Description

Version:

SwissGrip power grip with non-allergenic elastomer coating and a core of particularly tough and impact-resistant polypropylene. High torques can be exerted even with wet and oily hands. **Blade** of PB Swiss Tools special alloy combines maximum hardness with exceptional toughness. Surface nickel-plated and chrome-plated. Black tip. Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.

Tool handle made of conductive plastic, **suitable for ESDs**.

Advantage:

- **Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.**
- **No cam-out effect.**
- **Tips perfectly fit standard and non-standard screw slot sizes.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

Application:

For repair and assembly work, for loosening tight screws etc.

Technical description

| | |
|-------------------|-------|
| Blade designation | 0 |
| Blade length | 80 mm |

| | |
|------------------------------------|---------------------------------|
| Blade width b | 2.5 mm |
| Actuation hexagon through blade | no |
| Blade tip | black |
| overall length | 160 mm |
| Tip thickness a | 0.4 mm |
| Series | SwissGrip ESD |
| electrostatic characteristic | EGB/ESD |
| Drive profile | Slot-head screwdriver |
| Type of shank | round |
| Impact cap | no |
| Material | PB Swiss Tools special alloy |
| Surface | nickel-plated and chrome-plated |
| Type of product | Screwdrivers |