

**Universal abrasive cleaner, 80×50×20 mm, Type: M****Order data**

Order number	557660 M
GTIN	4045197241764
Item class	52E

Description**Version:**

Flexible hand abrasive block with flexibly bonded abrasive grit (long service life, fully usable). Open pore bonding ensures the abrasive body never clogs. Suitable for wet and dry use. Water and oil resistant.

Economy version with aluminium oxide (A).

Application:

Multi-purpose for **cleaning, polishing, smoothing, mat finishing** and **abrading all materials**.

Note:

Water, oil, compounds or similar agents **increase the effectiveness**.

Technical description

Grit designation	medium
Height	20 mm
Width	50 mm
Length	80 mm
Product name attribute	80×50×20 mm
Type of product	Sanding block

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
Stone	suitable		
Paint	suitable		
wet maximum	suitable		
dry	suitable		