



Abrasive cloth (A) economy roll, blue, normal KK 24, 40 mm × 50 m., Grit: 150



Order data

| | |
|--------------|---------------|
| Order number | 557710 150 |
| GTIN | 4018875266977 |
| Item class | 56V |

Description

Version:

Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A)**. Very good grit bonding, high abrasion performance and long service life.

Type **VSM KK 24: Blue fabric, low cost abrasive cloth roll** for normal applications.

Packaging tape **with integral tear-off cutter**.

Application:

Predominantly for rubbing down metals by hand, but also suitable for all other materials.

Technical description

| | |
|----------------------|------------------------------|
| Grit | 150 |
| Grit designation | medium |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |
| Economy roll width | 40 mm |
| Economy roll length | 50 m |

| | |
|------------------------|----------------|
| Product name attribute | 40 mm × 50 m. |
| Type of product | Abrasive cloth |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |