

3M**Ear defenders Peltor™ LiteCom™****Order data**

Order number	097798
GTIN	4046719783694
Item class	04A

Description**Version:**

Passive noise protection headset with integral radio device in the ear defenders. The incorporated two-way radio technology allows communication with other LiteCom™ ear defenders and radio devices. The **noise suppressing dynamic voice microphone** permits a simplified communication even in noisy environments. Very high power permits a range is up to three kilometres. The headset works with the licence-exempt PMR 446 standard and therefore has precisely 8 channels in the frequency range of 446 MHz. The three buttons allow **easy operation**.even when wearing gloves. **Voice-activated transmission (VOX)** without pressing any buttons and auto-off function. SNR = 32 dB (H = 33 dB, M = 30 dB, L = 23 dB).

Combines hearing protection, headphones and microphone.

Application:

For communication in noisy working environments.

Standard:

EN 352-1; EN 352-6

Supplied with:

Supplied with 2× AA batteries (alkaline-manganese) 081556 LR6.

Note:

Hygiene sets are listed under No. 097767 size HY79.

SNR value (noise attenuation): 32 dB(A)

Working time: 20 h

Weight: 394 g

Technical description

SNR value (noise attenuation)	32 dB(A)
Working time	20 h
Series	Peltor™ LiteCom™
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081556 LR6
Weight	394 g
Power supply	Battery-powered
Standard	EN 352-6
Standard	EN 352-1
Type of product	Ear defenders

Accessories

Noise indicator NI100	097305
Storage box	096920
Alkaline-manganese batteries International size LR6	081556 LR6
Hygiene kit Type HY79	097767 HY79