

**HOLEX**

**Heavy-duty combination pliers, bright finish, with two-component grips,  
Overall length: 180mm**



## Order data

Order number	700445 180
GTIN	4045197882325
Item class	72B

## Description

**Version:**

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); suitable even for piano wire. Jaws bright finished, handles with multi-component covering.

**Standard:**

**DIN ISO 5746.**

**Material:**

Special tool steel, drop-forged and oil-hardened.

## Technical description

Cutting capacity piano wire up to Ø	2 mm
Cutting capacity hard wire up to Ø	2.5 mm
overall length	180 mm
Standard	DIN ISO 5746
Handle	2-component grip
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel
Surface	bright finish

non-sparking	no
Type of product	Multi-function pliers