

**Garant**
**Self-tightening high-performance drill chuck with MT shank, MT shank: 4**

**Order data**

Order number	341122 4
GTIN	4045197880758
Item class	31K

**Description**
**Version:**

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

- **Drill chuck and MT shank are a single unit.**
- **High concentricity, optimum stability.**
- **Easy and quick change due to short design, advantageous for confined working areas.**

**Application:**

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

**Standard:**
**DIN 238**
**Note:**

The self-tightening effect works only for clockwise rotation.

**Technical description**

L <sub>1</sub> open	86.5 mm
L <sub>1</sub> closed	99 mm
External Ø	50 mm
Clamping range	1 - 13 mm
Type of product	Drill chuck keyless

