



## LED rechargeable work lamp, Type: STAR



### Order data

Order number	081516 STAR
GTIN	5708997356203
Item class	08C

### Description

#### Version:

**LED rechargeable work lamp** with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. **Handy cordless work lamp** and floodlight combined in a single lamp. **Flexible handle** with built-in magnet, suitable for direct mounting on a Scangrip stand. Built-in power bank with USB socket. Without suspension hook.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with USB charging cable.

### Technical description

Power supply	Rechargeable battery powered
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Battery capacity	5.2 Ah

Battery voltage	3.7 V
Bulb	LED module
Illumination step 2	500 lm
Illumination	1000 lm
Overall width	103 mm
IP Index of Protection	IP 65
Overall length	156 mm
Illumination time stage 2	5 h
Illumination time	2.5 h
Weight	710 g
ATEX zone	no
Manufacturer's designation	STAR
Type of product	Work lamp