

**Garant****Screwdriver set, Number of pieces: 10****Order data**

Order number	667532 10
GTIN	4045197882394
Item class	61F

**Description****Version:**

**Power grip** with easy-to-hold, easy-grip **Haptoprene** surface and a core of particularly tough and impact-resistant polypropylene. Due to its special surface structure, the grip is non-slip even with oily or wet hands.

**Blade** of chrome vanadium special alloy combining maximum hardness and exceptional toughness. Surface nickel-plated and chrome-plated. Black tips, accurately dimensioned.

**Voltage tester** 110 – 250 V in accordance with VDE 0680/6.

**Content:**

Slot-head blades No. 659928: Size 4; 5.5; 6.5; 8

Blades for Phillips No. 659921: Sizes 1 and 2

Pozidriv blade No. 659923: Size 2

Reamer blade No. 667640: 1 pc.

Voltage tester No. 665010: Size 2.5

2-component plastic handle No. 667531: 1 pc.

**Supplied with:**

Textile roll-up wallet.

**Note:**

Spare blades can be found under No. 659921 – 659928.

**Technical description**

Drive profile	Slot-head screwdriver
---------------	-----------------------

Drive profile	Pozidriv screwdriver
Drive profile	Phillips screwdriver
Number of pieces	10
Type of product	Screwdrivers

### Accessories

Haptoprene® plastic grip	667531
Voltage tester special quality Blade width 2,5 mm	665010 2,5
Reamer bit	667640
6 mm blade for Phillips Cross-head size 2	659921 2
6 mm blade Slot-head Blade width 6,5 mm	659928 6,5
6 mm blade Slot-head Blade width 8 mm	659928 8
6 mm blade Slot-head Blade width 4 mm	659928 4
6 mm blade Pozidriv Cross-head size 2	659923 2
6 mm blade for Phillips Cross-head size 1	659921 1
6 mm blade Slot-head Blade width 5,5 mm	659928 5,5