



## External micrometer Inch graduations, Measuring range: 1-2



### Order data

|              |               |
|--------------|---------------|
| Order number | 420650 1-2    |
| GTIN         | 4045197882585 |
| Item class   | 42B           |

### Description

#### Version:

With hand temperature protection.

**Precision lapped, carbide-tipped measuring faces.** Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

#### Supplied with:

From size 1-2 including 1 setting standard.

### Technical description

|                        |                          |
|------------------------|--------------------------|
| Spindle Ø              | 6.5 mm                   |
| Barrel Ø               | 18 mm                    |
| Scale divisions        | 0.0001 in                |
| Measuring range        | 1 - 2 in                 |
| Standard               | Manufacturer's standard  |
| Calibration            | B2                       |
| Measurement technology | analogue                 |
| Packaging              | sturdy box               |
| Type of product        | External tube micrometer |

### Services

DAkkS calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022050 100

Calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022040 100

---

## Accessories

Micrometer setting standard overall length 1

421150 1