



## External micrometer Inch graduations, Measuring range: 2-3



### Order data

Order number	420650 2-3
GTIN	4045197882592
Item class	42B

### Description

#### Version:

With hand temperature protection.

**Precision lapped, carbide-tipped measuring faces.** Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

#### Supplied with:

From size 1-2 including 1 setting standard.

### Technical description

Spindle Ø	6.5 mm
Barrel Ø	18 mm
Calibration	B2
Calibration	B2
Scale divisions	0.0001 in
Measuring range	2 - 3 in
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

DAkkS calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022050 100

Calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022040 100

---

## Accessories

Micrometer setting standard overall length 2

421150 2