



COLOUR MATCH LED true colour work light, Type: SUN2



Order data

Order number	081513 SUN2
GTIN	5708997354452
Item class	08C

Description

Version:

COLOUR MATCH. Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **SUNMATCH.** Rechargeable **dust-proof and waterproof** cordless work lamp. With sturdy swivel hook and powerful built-in magnet. Flexible lamp head (swings through 180°). Up to **3 hours operation** using the two-stage switch. **Intelligent protective circuit** switches off after 3 minutes if the lamp is set to full power. Charging station ready for wall mounting and magnet for attaching to the workbench.

SUNMATCH. Rechargeable **dust-proof and waterproof** cordless work lamp. With sturdy swivel hook and powerful built-in magnet. Flexible lamp head (swings through 180°). Up to **3 hours operation** using the two-stage switch. **Intelligent protective circuit** switches off after 3 minutes if the lamp is set to full power. Charging station ready for wall mounting and magnet for attaching to the workbench.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Charger, USB cable, 3.7 V / 2600 mAh Li-ion battery.

Technical description

Battery voltage	3.7 V
Illumination	500 lm
Power supply	Rechargeable battery powered
Number of rechargeable batteries contained	1
Light colour	warm-white
Light colour	cold-white
Light colour	true colour
Colour temperature	4500 - 6500 K
Type of rechargeable battery	Lithium-ion
Battery capacity	2.6 Ah
CRI value	96
IP Index of Protection	IP 65
Overall width	60 mm
Illumination time	2 h
Overall length	190 mm
Weight	300 g
ATEX zone	no
Type of product	Work lamp

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/081513-SUN2>