

**Three square file, Cut 2 (2nd cut), Length without tang: 300mm****Order data**

Order number	511200 300
GTIN	4009215017281
Item class	56B

Description**Version:**

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

Cuts on all faces; convex end.**Application:**

The **quality file** for workshop use with long tool life and high removal rate.

Standard:**DIN 7261 Form C****Note:**

File version with handle available under No. 511201.

Technical description

Length without tang	300 mm
Width	21 mm
Product name attribute	Cut 2 (2nd cut)
Cut	2
Type of cut	2nd cut
Shape	C
Shape description	three-square, taper plain end
File surfaces	3
incl. file handle	no
Standard	DIN 7261

Type of product

Engineer's file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		

Accessories

Hardwood file handle Overall length 160 mm	519400 160
Plastic file handle Overall length 120 mm	519550 120
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
Plastic file handle Overall length 125 mm	519510 125
2-component ergonomic file handle Overall length 120 mm	519600 120
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
File brush Bristle length L3× width L1 80X20 mm	576000 80X20