



Stereo microscope, Type: A60S



Order data

Order number	491782 A60S
GTIN	7630003566154
Item class	49B

Description

Version:

StereoZoom microscope with a magnification range from 5× to 30×, allowing both detail viewing and also a general overview. Thanks to the patented FusionOptics™ technology, the Leica A60 achieves a depth of focus of 13.6mm at the lower zoom step which avoids tedious refocussing when viewing higher components.

- **Unrivalled depth of focus (13.6 mm).**
- **46 mm object field.**
- **Ergonomic working due to the high working distance (122 mm).**
- **Antistatic plastic casing.**
- **Including LED ring light with 10 brightness steps.**
- **Clip-on diffuser (removable) for reduction in reflections.**

With swing arm stand.

- **For repeating objects.**
- **Direct earthing point in the base.**
- **Particularly high stability for working at high magnifications.**

Application:

Ideal for industrial inspections, assembly, and quality control.

Supplied with:

Mains cable.

Optional extras:

Transillumination No. 491777 size BLI.

Technical description

LED illumination system	16 Med Power SMT LEDs
Base width	266 mm
Optics system	Greenough with Fusion Optics™
maximum throat depth	560 mm
Field of vision Ø	46 mm
Zoom	6: 1
maximum depth of focus	13.6 mm
Working distance	122 mm
Colour temperature of incident light	5600 K
Magnification (x-times)	5 - 30
Angle of view	38 degrees
Base length	230 mm
Power supply	Mains operated
Type of product	Stereo microscope

Accessories

Transillumination Type BLI	491777 BLI
----------------------------	------------